


**Transport equipment**

# Product data sheet

Article no.: 4614-1AS Trolley with carrier spars with anti skidding device



Modular system: Frame made of sturdy square tube. Cross beams, posts and bars connected with solid screwed joints. Carrier spars made of tubular steel  $\varnothing$  27 mm with screwed joints. With 12 one-side carrier spars coated with PVC hose and with anti skidding device. Carrying capacity per level 80 kg. Powder coated blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to EN 1757-3.

## Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Length of usable platform (mm)</b>	1200
<b>Width of usable platform (mm)</b>	800
<b>Total length (mm)</b>	1400
<b>Total width (mm)</b>	800
<b>Total height (mm)</b>	1807
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	einseitig
<b>Weight (kg)</b>	72,5
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976983066