


Transport equipment

Product data sheet

Article no.: 4616 Trolley with carrier spars



Modular system: Frame made of sturdy square tube. Cross beams, posts and bars connected with solid screwed joints. Carrier spars made of tubular steel \varnothing 27 mm with screwed joints. With 12 one-side carrier spars. Carrying capacity per level 80 kg. Powder coated blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to EN 1757-3.

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	2000
Width of usable platform (mm)	800
Total length (mm)	2200
Total width (mm)	800
Total height (mm)	1807
Tyres	TPE
Wheel size (mm)	200 x 40
Version	einseitig
Weight (kg)	77
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976046167