


**Transport equipment**

# Product data sheet

Article no.: 4625-1AS Trolley with carrier spars with anti skidding device



Modular system: Frame made of sturdy square tube. Cross beams, posts and bars connected with solid screwed joints. Carrier spars made of tubular steel  $\varnothing$  27 mm with screwed joints. With 24 carrier spars on both sides (12 per side) coated with PVC hose and with anti skidding device. Carrying capacity per level 120 kg (60 kg per side). Powder coated blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to EN 1757-3.

## Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Length of usable platform (mm)</b>	1600
<b>Width of usable platform (mm)</b>	800
<b>Total length (mm)</b>	1800
<b>Total width (mm)</b>	800
<b>Total height (mm)</b>	1807
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	zweiseitig
<b>Weight (kg)</b>	77
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976983141