


**Transport equipment**

# Product data sheet

Article no.: 4626 Trolley with carrier spars



Modular system: Frame made of sturdy square tube. Cross beams, posts and bars connected with solid screwed joints. Carrier spars made of tubular steel  $\varnothing$  27 mm with screwed joints. With 24 carrier spars on both sides (12 per side). Carrying capacity per level 120 kg (60 kg per side). Powder coated blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to EN 1757-3.

## Technical Details:



|                                       |               |
|---------------------------------------|---------------|
| <b>Total load capacity (kg)</b>       | 500           |
| <b>Length of usable platform (mm)</b> | 2000          |
| <b>Width of usable platform (mm)</b>  | 800           |
| <b>Total length (mm)</b>              | 2200          |
| <b>Total width (mm)</b>               | 800           |
| <b>Total height (mm)</b>              | 1807          |
| <b>Tyres</b>                          | TPE           |
| <b>Wheel size (mm)</b>                | 200 x 40      |
| <b>Version</b>                        | zweiseitig    |
| <b>Weight (kg)</b>                    | 75            |
| <b>Country of origin</b>              | Germany       |
| <b>Warranty (years)</b>               | 10            |
| <b>Customs tariff number</b>          | 87168000      |
| <b>GTIN</b>                           | 4017976046266 |