


Transport equipment

Product data sheet

Article no.: 4701 Sheet metal dump truck without drainage tap



Made of 2 mm thick steel sheet, with double-folded top rim. Welded oil-tight. Chassis made of 3 mm thick canted steel sheet, with integrated stacker pockets. Kickplate and tilt lock, tubular steel handle. Powder coated blue RAL 5007. Fitted with 2 swivel and 2 fixed-wheel castors. Wheels with TPE tyres, 200 x 40 mm, hubs with groove ball bearing. Equipped as standard with TOTALSTOP - central brake system on swivel castors, according to the European Standard EN 1757-3 (safety of platform trolleys). Moveable by hand pushing and forklifters. Without drainage tap and sieve. Tipping process is triggered manually. For emptying with a forklift truck or for heavy loads, we recommend a tipping container or a self-tilting box.

Technical Details:



Total load capacity (kg)	750
Content (litres)	250
Box dimensions (mm)	1200 x 652 x 413
Dumping edge height with wheels (mm)	780
Total length (mm)	1359
Total width (mm)	713
Total height (mm)	780
Tyres	TPE
Wheel size (mm)	200 x 40
Version	ohne Ablasshahn
Weight (kg)	70
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976047010