


**Transport equipment**

# Product data sheet

Article no.: 47D3/7016 Cover for sheet metal dump trucks



Hinged cover for dump truck, can be opened on 2 sides. When closed, the cover can be locked in place with spring hooks. When flipped open, the front part can be secured with spring hooks to prevent unwanted slamming during tilting. The flipped open back part of the cover can also be locked in place. Folded handle rail on front and back of the cover. Steel sheet 1.5 mm, internally reinforced with 15 x 3 mm steel strip braces. No external protrusions to avoid any shearing risk. Powder coated in blue RAL 5007 or anthracite RAL 7016. Can be retro-fitted. Surcharge per dump truck.

## Technical Details:



<b>Total length (mm)</b>	1321
<b>Total width (mm)</b>	794
<b>Colour</b>	anthracite grey
<b>Note</b>	for sheet metal dump trucks 4703
<b>Weight (kg)</b>	17,5
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976534763