


Transport equipment

Product data sheet

Article no.: 47D3 Cover for sheet metal dump trucks



Hinged cover for dump truck, can be opened on 2 sides. When closed, the cover can be locked in place with spring hooks. When flipped open, the front part can be secured with spring hooks to prevent unwanted slamming during tilting. The flipped open back part of the cover can also be locked in place. Folded handle rail on front and back of the cover. Steel sheet 1.5 mm, internally reinforced with 15 x 3 mm steel strip braces. No external protrusions to avoid any shearing risk. Powder coated in blue RAL 5007 or anthracite RAL 7016. Can be retro-fitted. Surcharge per dump truck.

Technical Details:



Total length (mm)	1321
Total width (mm)	794
Colour	blue
Note	for sheet metal dump trucks 4703
Weight (kg)	17,5
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976534725