


Transport equipment

Product data sheet

Article no.: 4882 Office trolley



Modular system: bolted, tubular steel construction, powder coated light grey RAL 7035. 3 shelves of derived material timber board, pale grey. 4 swivel castors with TPE tyres, hubs with roller bearings. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed for easy self assembly.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	800
Width of usable platform (mm)	500
Shelf heights (mm)	260, 530, 800
Load capacity per shelf (kg)	50
Total length (mm)	900
Total width (mm)	535
Total height (mm)	925
Tyres	TPE
Wheel size (mm)	125 x 32
Version	offen
Weight (kg)	24
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976048826