


Transport equipment

Product data sheet

Article no.: 4891 Office trolley



Modular system: Office trolley with shelves inclined to the rear. Back wall in a right angle to the shelf. Inclination approx. 27 mm. Bolted, tubular steel construction, powder coated light grey RAL 7035. Shelves and panels made of derived material timber board, pale grey. 4 swivel castors with TPE tyres, hubs with roller bearings. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed for easy self assembly.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	770
Width of usable platform (mm)	320
Shelf heights (mm)	246, 606, 1016
Load capacity per shelf (kg)	50
Total length (mm)	855
Total width (mm)	400
Total height (mm)	1218
Tyres	TPE
Wheel size (mm)	125 x 32
Version	mit Rückwand
Weight (kg)	31
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976348919