


Transport equipment

Product data sheet

Article no.: 5019 Stainless steel trolley



Stainless steel trolley (tea-cart) with tubular push bar made of CNS (chrome-nickel steel) and 3 deep-drawn shelves made of CS (chrome steel), with all-round skirting, lined for sound reduction. Capacity per shelf 80 kg. 4 swivel castors with TPE wheels, elastic and easy running, trackless. Hubs with ball bearings, 2 swivel castors with wheel locks according to the European Standard EN 1757-3 (safety of platform trolleys). Rustproof wheels according to DIN 18867 part 8. For preventing large damages with protective edges and protective wheels. Flat packed for easy self assembly.

Technical Details:



Total load capacity (kg)	150
Shelf heights (mm)	230, 540, 850
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Total length (mm)	1070
Total width (mm)	670
Total height (mm)	950
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	22
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976150192