


Transport equipment

Product data sheet

Article no.: 5038 Stainless steel trolley



Stainless steel trolley (tea-cart) with tubular push bar made of CNS (chrome-nickel steel) and 3 deep-drawn shelves made of CS (chrome steel), with all-round skirting, lined for sound reduction. Capacity per shelf 80 kg. 4 swivel castors with TPE wheels, elastic and easy running, trackless. Hubs with ball bearings, 2 swivel castors with wheel locks according to the European Standard EN 1757-3 (safety of platform trolleys). Rustproof wheels according to DIN 18867 part 8. For preventing large damages with protective edges and protective wheels. Flat packed for easy self assembly.

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 150 |
| Shelf heights (mm) | 230, 540, 850 |
| Length of usable platform (mm) | 630 |
| Width of usable platform (mm) | 400 |
| Total length (mm) | 700 |
| Total width (mm) | 470 |
| Total height (mm) | 950 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 14,5 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976150383 |