


Transport equipment

Product data sheet

Article no.: 5834 Rolling desk



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Surface made of derived timber material, 605 mm wide und 590 mm deep, with stop bar. 2 screw-down shelves, upper shelf centred shrewable for the possiility of 2 folders on top of each other. Capacity per shelf 50 kg. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Easy movement across angles and barriers because of the big wheels.

Technical Details:



Total load capacity (kg)	100
Surface height (mm)	1100, 1195
Length of usable platform (mm)	600
Width of usable platform (mm)	500
Total width (mm)	605
Total depth (mm)	610
Total height (mm)	1195
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	25
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976658346