


**Transport equipment**

# Product data sheet

Article no.: 5837 Rolling desk



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Surface made of derived timber material, 1100 mm wide und 590 mm deep, with stop bar. 2 screw-down shelves, upper shelf centred shrewable for the possiility of 2 folders on top of each other. Capacity per shelf 50 kg. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Easy movement across angles and barriers because of the big wheels.

## Technical Details:



<b>Total load capacity (kg)</b>	100
<b>Surface height (mm)</b>	1100, 1195
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Total width (mm)</b>	1105
<b>Total depth (mm)</b>	610
<b>Total height (mm)</b>	1195
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	39
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	94032080
<b>GTIN</b>	4017976658377