


Transport equipment

Product data sheet

Article no.: 5862 Rolling table



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Table board made of beech plywood, 20 mm thick, surface out of beech decoration. 2 screw-down shelves, variable distance of 50 mm, 1 x folder height possible. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Capacity per shelf 50 kg. Table height 910 mm. Screw-down shelves 300 und 670 mm high, variable distance of 50 mm.

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 150 |
| Length of usable platform (mm) | 1120 |
| Width of usable platform (mm) | 650 |
| Shelf heights (mm) | 300, 670, 910 |
| Load capacity per shelf (kg) | 50 |
| Total width (mm) | 1120 |
| Total height (mm) | 910 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 42 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 94032080 |
| GTIN | 4017976058627 |