


Transport equipment

Product data sheet

Article no.: 5864 Rolling table



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Table board made of beech plywood, 20 mm thick, surface out of beech decoration. 2 screw-down shelves, variable distance of 50 mm, 1 x folder height possible. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Capacity per shelf 50 kg. Table height 910 mm. Screw-down shelves 300 und 670 mm high, variable distance of 50 mm. With 1 lockable steel cupboard with leafdoor, 1 fixed and 2 adjustable shelves. Width 500 mm, Depth 600 mm, Height 600 mm. Powder coated, carcass RAL 7035, blue front RAL 5007.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	1120
Width of usable platform (mm)	650
Shelf heights (mm)	300, 670, 910
Load capacity per shelf (kg)	50
Total width (mm)	1120
Total height (mm)	910
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	59
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976058641