


Transport equipment

Product data sheet

Article no.: 5868 Rolling table



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Table board made of beech plywood, 20 mm thick, surface out of beech decoration. 2 lockable steel cupboards. Capacity per shelf in cupboards 30 kg. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Capacity per shelf 50 kg. Table height 910 mm. Screw-down shelves 300 und 670 mm high, variable distance of 50 mm.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	1120
Width of usable platform (mm)	650
Shelf heights (mm)	910
Load capacity per shelf (kg)	30
Total width (mm)	1120
Total height (mm)	910
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	76
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976058689