


**Transport equipment**

# Product data sheet

Article no.: 6250 Tipping container without drainage tap



Particularly low construction. Tipping containers must be lifted with a fork lift for emptying. By dropping the box to the ground the container will be adjusted automatically and moved back into loading position. Sturdy welded 2 mm sheet steel design, powder coated in RAL 5007 blue. Standard-fitted fork-lift sleeves, anti-roll safety device and tilt lock. Safety chain as anti-skidding and safety device. Traction cable to activate tilting mechanism, operated from fork-lift truck driver's seat. Item number with addition "A" means "with drainage tap".

## Technical Details:



<b>Total load capacity (kg)</b>	1000
<b>Content (litres)</b>	500
<b>Box dimensions (mm)</b>	1164 x 831 x 598
<b>Dumping edge height without wheels (mm)</b>	519
<b>Dumping edge height with wheels (mm)</b>	756
<b>Total length (mm)</b>	1389
<b>Total width (mm)</b>	890
<b>Total height (mm)</b>	676
<b>Version</b>	ohne Ablasshahn
<b>Weight (kg)</b>	86
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73090090
<b>GTIN</b>	4017976656250