


Transport equipment

Product data sheet

Article no.: 6275 Tipping container without drainage tap



Particularly low construction. Tipping containers must be lifted with a fork lift for emptying. By dropping the box to the ground the container will be adjusted automatically and moved back into loading position. Sturdy welded 2 mm sheet steel design, powder coated in RAL 5007 blue. Standard-fitted fork-lift sleeves, anti-roll safety device and tilt lock. Safety chain as anti-skidding and safety device. Traction cable to activate tilting mechanism, operated from fork-lift truck driver's seat. Item number with addition "A" means "with drainage tap".

Technical Details:



Total load capacity (kg)	1000
Content (litres)	750
Box dimensions (mm)	1164 x 1241 x 598
Dumping edge height without wheels (mm)	519
Dumping edge height with wheels (mm)	756
Total length (mm)	1390
Total width (mm)	1300
Total height (mm)	676
Version	ohne Ablasshahn
Weight (kg)	108
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73090090
GTIN	4017976662756