


**Transport equipment**

# Product data sheet

Article no.: 6403V Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with solid rubber tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3.

## Technical Details:



<b>Total load capacity (kg)</b>	750
<b>Length of usable platform (mm)</b>	1200
<b>Width of usable platform (mm)</b>	800
<b>Height of loading platform (mm)</b>	420
<b>Total length (mm)</b>	1545
<b>Total width (mm)</b>	800
<b>Total height (mm)</b>	1125
<b>Tyres</b>	Solid rubber
<b>Wheel size (mm)</b>	260 x 56
<b>Version</b>	offen
<b>Weight (kg)</b>	66
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976014012