


Transport equipment

Product data sheet

Article no.: 6404LZ Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with pneumatic tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3.

Technical Details:



Total load capacity (kg)	1000
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	490
Total length (mm)	1545
Total width (mm)	800
Total height (mm)	1200
Tyres	Pneumatic
Wheel size (mm)	400 x 100
Version	offen
Weight (kg)	68
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976214030