


Transport equipment

Product data sheet

Article no.: 6404VZ Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with solid rubber tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3.

Technical Details:



| | |
|--|---------------|
| Total load capacity (kg) | 1000 |
| Length of usable platform (mm) | 1200 |
| Width of usable platform (mm) | 800 |
| Height of loading platform (mm) | 490 |
| Total length (mm) | 1545 |
| Total width (mm) | 800 |
| Total height (mm) | 1190 |
| Tyres | Solid rubber |
| Wheel size (mm) | 400 x 74 |
| Version | offen |
| Weight (kg) | 89 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976214221 |