


Transport equipment

Product data sheet

Article no.: 6444L Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with pneumatic tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3. Boards 1000 mm high, sides screwed on platform, Sides mountable and removable. Tubular steel frame with welded wire lattice 40 x 40 x 4 mm, powder coated blue RAL 5007.

Technical Details:



| | |
|--|-----------------------|
| Total load capacity (kg) | 1000 |
| Length of usable platform (mm) | 1200 |
| Width of usable platform (mm) | 800 |
| Height of loading platform (mm) | 490 |
| Total length (mm) | 1550 |
| Total width (mm) | 850 |
| Total height (mm) | 1490 |
| Tyres | Pneumatic |
| Wheel size (mm) | 400 x 100 |
| Version | mit Drahtgitterwänden |
| Weight (kg) | 108 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976444017 |