


Transport equipment

Product data sheet

Article no.: 6455V Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with solid rubber tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3. Boards 250/325 mm high, 3 sides tilting, front end fixed. Powder coated tubular steel frame with waterproof plywood platform.

Technical Details:



Total load capacity (kg)	1000
Length of usable platform (mm)	1600
Width of usable platform (mm)	900
Height of loading platform (mm)	490
Total length (mm)	1960
Total width (mm)	925
Total height (mm)	1190
Tyres	Solid rubber
Wheel size (mm)	400 x 74
Version	mit Bordwänden
Weight (kg)	118
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976014111