


**Transport equipment**

# Product data sheet

Article no.: 6855 Hydraulic hand stacker



For the occasional use as lifting and transport appliance. Sturdy sectional steel construction with tubular push handles, powder coated anthracite RAL 7016. Hydraulic pump with chromiumplated piston and overload valve. Operated via drawing shaft. Lowering valve precisely adjustable via hand lever. 2 castor wheels, wheels with Polyurethane tyres 150 x 40 mm and 2 fork rollers nylon 80 x 70 mm. Castor wheels with lock. Load center distance: 585 mm, stroke per shaft operation: 20 mm, total height: 2010 mm.

## Technical Details:

<b>Total load capacity (kg)</b>	500
<b>Total length (mm)</b>	1600
<b>Total width (mm)</b>	794
<b>Total height (mm)</b>	2010
<b>Lifting range (mm)</b>	88 - 1500
<b>Fork length (mm)</b>	1150
<b>Fork width (m)</b>	160
<b>Loading width (mm)</b>	540
<b>Tyres</b>	Polyurethane
<b>Wheel size (mm)</b>	150 x 40
<b>Material fork rollers</b>	Nylon
<b>Fork rollers diameter x width (mm)</b>	80 x 70
<b>Weight (kg)</b>	210
<b>Country of origin</b>	China
<b>Warranty (years)</b>	2
<b>Customs tariff number</b>	84279000
<b>GTIN</b>	4017976068558