

**Transport equipment**

Product data sheet

Article no.: 6890 Roller conveyor



Sectional steel frame with holding angles and 2 upward tilting stops, powder coated anthracite RAL 7016. 9 steel rolls (Ø 57 mm and length 430 mm) with roller bearings. Distance between axles 112,5 mm, height 64 mm, carrying capacity 500 kg - rigid-

Technical Details:

Total load capacity (kg)	500
Total height (mm)	64
Colour	anthracite grey
Note	for platform size 1010 x 520 mm
Weight (kg)	31
Country of origin	China
Warranty (years)	2
Customs tariff number	84283920
GTIN	4017976068909