


Transport equipment

Product data sheet

Article no.: 6891 Roller conveyor



Can be fixed to platform with clamped joint, swivelling by 360°, arrestable. 6 steel rolls (∅ 57 mm and length 430 mm) with roller bearings. Distance between axles: 110 mm
Height 92 mm, carrying capacity 500 kg - swivelling -

Technical Details:

Total load capacity (kg)	500
Total height (mm)	92
Colour	anthracite grey
Note	for platform size 1010 x 520 mm
Weight (kg)	51
Country of origin	China
Warranty (years)	2
Customs tariff number	84283920
GTIN	4017976068916