


**Transport equipment**

# Product data sheet

Article no.: 6953 Moving gear adjustable



Moving gear for the easy and safe transport of machines and other heavy goods. Sturdy welded steel construction with handles made of round steel, powder coated blue RAL 5007. Carrying platforms with anti-slip rubber cover. Big steel wheels with ball bearings. Scope of delivery: 2 transport rollers and 2 connecting rods made of round steel. Warranty: 2 years.

## Technical Details:

<b>Total load capacity (kg)</b>	24000
<b>Total length (mm)</b>	495
<b>Total width (mm)</b>	288
<b>Total height (mm)</b>	110
<b>Length of usable platform (mm)</b>	425
<b>Width of usable platform (mm)</b>	220
<b>Number of axes</b>	4
<b>Number of rolls</b>	16
<b>Wheel size (mm)</b>	83 x 85
<b>Tyres</b>	Steel
<b>Note</b>	adjustable range: 850 - 1190 mm
<b>Weight (kg)</b>	88
<b>Country of origin</b>	China
<b>Warranty (years)</b>	2
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976069531