


**Transport equipment**

# Product data sheet

Article no.: 6980 Furniture lifting rollers



Manual crank for one man transport of cupboards, lockers etc. Steel tubular construction, powder coated blue RAL 5007. Winch with manual crank arm. Crank protected by a C-profile. Adjustable supports with protective covering. Loading surface with anti-slip covering. Two steering wheels with non-marking Polyurethane tyres and non-tracking elasticated solid rubber tyres, hub with roller bearings. One fixed 5 m long strap. Delivered in pairs.

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Total length (mm)</b>	600
<b>Total width (mm)</b>	390
<b>Total height (mm)</b>	800
<b>Lifting range (mm)</b>	10 - 300
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	160 x 50
<b>Note</b>	carrying plate 300 x 110 mm
<b>Weight (kg)</b>	45
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976069807