


Transport equipment

Product data sheet

Article no.: 71253 Swivel castor

Casings made of steel sheet, galvanized. Wheels with elastic tyres, blue-grey, non-marking (trackless). Alu-rims, hubs with ball bearings. Smooth, silent running, long durability.



Technical Details:

Total load capacity (kg)	300
Wheel size (mm)	160 x 50
Tyres	Elastic solid rubber blue grey
Effective height (mm)	196
Mounting plate (mm)	135 x 110
Screw hole distances (mm)	105 x 75/80
Screw hole-Ø (mm)	11
Weight (kg)	2,52
Country of origin	China
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976671253