


Transport equipment

Product data sheet

Article no.: 8303 Shelved trolley



Modular system: Shelved trolleys made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends of tubular construction, open. 1 fix and 3 variable shelves made of special wood material boards, surface beech grain. Variable use of shelves, in a grid of 100 mm. Capacity of shelf 90 kg. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Load capacity per shelf (kg)	90
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Total length (mm)	1369
Total width (mm)	809
Total height (mm)	1800
Shelf heights (mm)	269, 669, 1069, 1469
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	86
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976083032