


Transport equipment

Product data sheet

Article no.: 8581-3DE Shelved trolley with wing doors



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends and 1 side made of wire lattice 100 x 100 x 5 mm. With roof made of wire lattice and with double wing doors at the open side panel. Tubular steel frame with wire lattice 100 x 100 x 5 mm. Integrated bolt lock, doors lockable with padlock (not included in delivery), wing doors turnable till side panels. 1 fix and 4 variable shelves made of special wood material boards, surface beech grain. Variable use of shelves, in a grid of 100 mm. Capacity of shelf 90 kg. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Load capacity per shelf (kg)	90
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Total length (mm)	1169
Total width (mm)	630
Total height (mm)	1800
Shelf heights (mm)	269, 569, 869, 1169, 1469
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	104
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976785813