


**Transport equipment**

# Product data sheet

Article no.: 8343 Shelved trolley



Modular system: Shelved trolleys made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends of tubular construction, open. 1 fix and 4 variable shelves made of special wood material boards, surface beech grain. Variable use of shelves, in a grid of 100 mm. Capacity of shelf 90 kg. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



|                                       |                           |
|---------------------------------------|---------------------------|
| <b>Total load capacity (kg)</b>       | 600                       |
| <b>Load capacity per shelf (kg)</b>   | 90                        |
| <b>Length of usable platform (mm)</b> | 1200                      |
| <b>Width of usable platform (mm)</b>  | 800                       |
| <b>Total length (mm)</b>              | 1369                      |
| <b>Total width (mm)</b>               | 809                       |
| <b>Total height (mm)</b>              | 1800                      |
| <b>Shelf heights (mm)</b>             | 269, 569, 869, 1169, 1469 |
| <b>Tyres</b>                          | TPE                       |
| <b>Wheel size (mm)</b>                | 200 x 40                  |
| <b>Weight (kg)</b>                    | 104                       |
| <b>Country of origin</b>              | Germany                   |
| <b>Warranty (years)</b>               | 10                        |
| <b>Customs tariff number</b>          | 87168000                  |
| <b>GTIN</b>                           | 4017976083438             |