


Transport equipment

Product data sheet

Article no.: 8352 Shelved trolley with tubes



Modular system: Shelved trolleys made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends of tubular construction with intermediate uprights at intervals of approx. 130 mm. 1 fix and 4 variable shelves made of special wood material boards, surface beech grain. Variable use of shelves, in a grid of 100 mm. Capacity of shelf 90 kg. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



| | |
|---------------------------------------|---------------------------|
| Total load capacity (kg) | 600 |
| Load capacity per shelf (kg) | 90 |
| Length of usable platform (mm) | 1000 |
| Width of usable platform (mm) | 700 |
| Total length (mm) | 1169 |
| Total width (mm) | 709 |
| Total height (mm) | 1800 |
| Shelf heights (mm) | 269, 569, 869, 1169, 1469 |
| Tyres | TPE |
| Wheel size (mm) | 200 x 40 |
| Weight (kg) | 94 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976083520 |