


**Transport equipment**

# Product data sheet

Article no.: 8411 Shelved trolley with wire lattice



Modular system: Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. End panels closed, made of wire lattice 100 x 100 x 5 mm. 1 fix and 3 variable shelves made of special wood material boards, surface beech grain. Variable use of shelves, in a grid of 100 mm. Capacity of shelf 90 kg. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Load capacity per shelf (kg)</b>	90
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Total length (mm)</b>	1169
<b>Total width (mm)</b>	609
<b>Total height (mm)</b>	1800
<b>Shelf heights (mm)</b>	269, 669, 1069, 1469
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	74
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976084114