


**Transport equipment**

# Product data sheet

Article no.: 8583-3D Parcel cart with double wing doors and roof



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends and 1 side made of wire lattice 100 x 100 x 5 mm. With roof made of wire lattice and with double wing doors at the open side panel. Tubular steel frame with wire lattice 100 x 100 x 5 mm. Integrated bolt lock, doors lockable with padlock (not included in delivery), wing doors turnable till side panels. Platform made of special wood material boards, surface beech grain. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1200
<b>Width of usable platform (mm)</b>	800
<b>Height of loading platform (mm)</b>	269
<b>Total length (mm)</b>	1369
<b>Total width (mm)</b>	830
<b>Total height (mm)</b>	1800
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	mit Türen und Dach
<b>Weight (kg)</b>	79
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976985831