


**Transport equipment**

# Product data sheet

Article no.: 9200 ESD-shelved trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. 1 fix and 2 variable shelves made of electrically conductive wooden material according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity per shelf 50 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Load capacity per shelf (kg)</b>	50
<b>Length of usable platform (mm)</b>	850
<b>Width of usable platform (mm)</b>	500
<b>Total length (mm)</b>	1019
<b>Total width (mm)</b>	509
<b>Total height (mm)</b>	1511
<b>Shelf heights (mm)</b>	235, 635, 1035, 1435
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	48
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976092003