


**Transport equipment**

# Product data sheet

Article no.: 92900 ESD-storage trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey RAL 7015. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. 2 swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Open frames without boards. Capacity upper and middle shelves 50 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	200
<b>Length of usable platform (mm)</b>	605
<b>Width of usable platform (mm)</b>	405
<b>Shelf heights (mm)</b>	197, 652, 1152
<b>Load capacity per shelf (kg)</b>	50
<b>Total length (mm)</b>	821
<b>Total width (mm)</b>	455
<b>Total height (mm)</b>	1178
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	23
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976929002