


Transport equipment

Product data sheet

Article no.: 9303 ESD-shelved trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. 1 fix and 3 variable shelves made of electrically conductive wooden material according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity per shelf 50 kg.

Technical Details:



Total load capacity (kg)	600
Load capacity per shelf (kg)	50
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Total length (mm)	1369
Total width (mm)	809
Total height (mm)	1800
Shelf heights (mm)	276, 676, 1076, 1476
Tyres	TPE-ESD
Wheel size (mm)	200 x 40
Weight (kg)	106
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976093031