


Transport equipment

Product data sheet

Article no.: 93540 ESD-euro box roller



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey RAL 7015. 4 swivel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. 2 castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). With 2 platforms with shelves made of electrically conductive (anti-static) wooden material, rim 7 mm high. Clearance between platforms 400 mm. Capacity upper shelf 100 kg. Suitable for euro boxes 600 x 400 mm.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	605
Width of usable platform (mm)	408
Shelf heights (mm)	201, 630
Load capacity per shelf (kg)	100
Total length (mm)	677
Total width (mm)	414
Total height (mm)	638
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	21
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976935409