


**Transport equipment**

# Product data sheet

Article no.: 93580 ESD-euro box roller



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey RAL 7015. Open angle steel construction. Suitable for euro boxes 600 x 400 mm. 4 swivel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. 2 castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	605
<b>Width of usable platform (mm)</b>	408
<b>Height of loading platform (mm)</b>	182
<b>Total length (mm)</b>	611
<b>Total width (mm)</b>	414
<b>Total height (mm)</b>	209
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	9
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976935805