


Transport equipment

Product data sheet

Article no.: 93581 ESD-euro box roller



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey RAL 7015. 4 swivel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. 2 castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Angle steel construction with platform made of electrically conductive (anti-static) wooden material, rim 7 mm high. Suitable for euro boxes 600 x 400 mm.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	605
Width of usable platform (mm)	408
Height of loading platform (mm)	201
Total length (mm)	611
Total width (mm)	414
Total height (mm)	209
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	12
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976935812