


**Transport equipment**

# Product data sheet

Article no.: 9384 ESD-euro box trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey, RAL 7015. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). With 5 platforms with shelves made of electrically conductive (anti-static) wooden material according to DIN 68765, light grey, rim 7 mm high. For 3 Euro boxes each 600 x 400 mm. Variable use of shelf frames, distance 50 mm, angle when inclined up to 15° and 30°. Capacity per shelf 80 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	1240
<b>Width of usable platform (mm)</b>	610
<b>Shelf heights (mm)</b>	317, 617, 917, 1217, 1517
<b>Load capacity per shelf (kg)</b>	80
<b>Total length (mm)</b>	1372
<b>Total width (mm)</b>	685
<b>Total height (mm)</b>	1686
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	123
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976493848