


Transport equipment

Product data sheet

Article no.: 9400 ESD-table top cart



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. 2 electrically conductive wooden shelves according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 200 kg.

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 500 |
| Length of usable platform (mm) | 850 |
| Width of usable platform (mm) | 500 |
| Shelf heights (mm) | 235, 867 |
| Total length (mm) | 1047 |
| Total width (mm) | 509 |
| Total height (mm) | 867 |
| Tyres | TPE-ESD |
| Wheel size (mm) | 160 x 40 |
| Weight (kg) | 38 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976494005 |