


Transport equipment

Product data sheet

Article no.: 9500 ESD-open trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. Electrically conductive wooden shelves according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Height of loading platform (mm)	235
Total length (mm)	970
Total width (mm)	509
Total height (mm)	950
Tyres	TPE-ESD
Wheel size (mm)	160 x 40
Weight (kg)	24
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976195001