


Transport equipment

Product data sheet

Article no.: AK1327 Stairway truck aluminium



Aluminium tube with aluminium blades, handy welded construction. Safety handles. Aluminum sheet shovel mountable. With 2 pneumatic tyres on synthetic rims, hubs with roller bearings and 2 five-armed wheel spiders, each equipped with 5 TPE wheels 125 mm Ø, hubs with bush bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Flat packed delivery.

Technical Details:



Total load capacity (kg)	200
Blade width (mm)	320
Blade depth (mm)	250
Total width (mm)	590
Total height (mm)	1300
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Version	für gelegentliche Treppenfahrten
Weight (kg)	15
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976113272