


Transport equipment

Product data sheet

Article no.: B1115V Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Solid rubber tyres on synthetic rims, hubs with roller bearings. Flat packed delivery.

Technical Details:



Total load capacity (kg)	250
Blade width (mm)	400
Blade depth (mm)	150
Total width (mm)	590
Total depth (mm)	506
Total height (mm)	1150
Tyres	Solid rubber
Wheel size (mm)	260 x 56
Weight (kg)	15
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976311159