


Transport equipment

Product data sheet

Article no.: B1215L Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Pneumatic tyres on synthetic rims, hubs with roller bearings. Flat packed delivery.

Technical Details:



Total load capacity (kg)	350
Blade width (mm)	450
Blade depth (mm)	150
Total width (mm)	620
Total depth (mm)	565
Total height (mm)	1200
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Weight (kg)	16
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976112152