


**Transport equipment**

# Product data sheet

Article no.: B1326L Tubular steel truck



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Pneumatic tyres on synthetic rims, hubs with roller bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Flat packed delivery.

## Technical Details:



<b>Total load capacity (kg)</b>	300
<b>Blade width (mm)</b>	480
<b>Blade depth (mm)</b>	300
<b>Total width (mm)</b>	580
<b>Total depth (mm)</b>	658
<b>Total height (mm)</b>	1300
<b>Tyres</b>	Pneumatic
<b>Wheel size (mm)</b>	260 x 85
<b>Weight (kg)</b>	16
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976513263