Product data sheet

Article no.: B1331L Tubular steel truck



Transport equipment



Handy tubular steel trucks with steel sheet blades, sturdy welded construction, blue RAL 5007. Safety grips. Steel sheet front shovel mountable, therefore exchangeable. Pneumatic tyres on synthetic rims, hubs with roller bearings. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Flat packed delivery.

Technical Details:





Total load capacity (kg)	300
Blade width (mm)	480
Blade depth (mm)	300
Total width (mm)	580
Total depth (mm)	677
Total height (mm)	1300
Tyres	Pneumatic
Tyres Wheel size (mm)	Pneumatic 260 x 85
Wheel size (mm)	260 x 85
Wheel size (mm) Weight (kg)	260 x 85 17
Wheel size (mm) Weight (kg) Country of origin	260 x 85 17 Germany
Wheel size (mm) Weight (kg) Country of origin Warranty (years)	260 x 85 17 Germany 10