


Transport equipment

Product data sheet

Article no.: B1345V Chair truck



For transporting stacked chairs. Made of tubular construction. A combination of stacking trolley B1325V with chair carrying facility. Sturdy welded construction, powder coated blue RAL 5007. Curved top bar and transversal struts. For safe transport of circular items such as rolls, cans, buckets etc. Safety grips, solid rubber tyres on synthetic rims, hubs with roller bearings. Carrier spar can be screwed with clamp to truck. After loosen the 2 screws the carrier spar can be continuously adjusted in height. The carrying arms are covered with protective hoses. Carrier arms: Length 500 mm, width 320 mm, capacity 70 kg

Technical Details:



Total load capacity (kg)	300
Blade width (mm)	320
Blade depth (mm)	250
Total width (mm)	580
Total depth (mm)	862
Total height (mm)	1300
Tyres	Solid rubber
Wheel size (mm)	260 x 56
Version	für Stühle
Note	Capacity carrying facility: 70 kg
Weight (kg)	19
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976813455